

At a glance

POWER OUTPUT

Up to 100 mW/cm²

Irradiance at 6 in · 45 W board draw

WAVELENGTHS

660 nm + 850 nm

Dual-chip LEDs (±10 nm) · UV-free

TREATMENT AREAS

Face to joints

Face, neck, shoulders, back, hips, legs

SESSION LENGTH

10 minutes

One session per area, up to 2× daily

Full specifications

LIGHT ENGINE

Wavelengths	660 nm red + 850 nm NIR
LED configuration	60 dual-chip LEDs
Beam angle	60°
Irradiance at 6 inches	~100 mW/cm ²

PHYSICAL

Dimensions	12 × 8 × 1.5 in
Weight	1.8 lb
Mounting	Handheld / travel pouch

USE & SOFTWARE

Session time	10 minutes
Protocols	Recovery, sleep, skin, focus
App connectivity	Bluetooth

SERVICE

Accessories in box	Travel pouch, power adapter, goggles
Shipping	Standard Australia-wide shipping fees apply
Returns	60-day returns in original condition
Delivery	Metro 2–4 days, regional 4–7 days

In the box

- Red light therapy panel
- Protective goggles
- Protocol quick-start guide
- 100–240 V power adapter
- Travel pouch

Safety

UV-free, non-invasive LEDs. Keep eyes closed or wear the included goggles during facial sessions.